


**Non-insulated**

| Applicable Wire mm <sup>2</sup> | Part No. | Nominal Size | Dimensions mm (in.) |             |            | Tool No.               | Qty/box |
|---------------------------------|----------|--------------|---------------------|-------------|------------|------------------------|---------|
|                                 |          |              | $\varnothing d_1$   | $\ell$      | s          |                        |         |
| 0.1 to <0.5                     | C-0.5A   |              | 1.2 (.047)          | 12.0 (.472) | 0.4 (.016) | WC-0510DIN             | 2,000   |
| 0.5 to 1                        | GSC-1    | 1            | 1.6 (.063)          | 15.0 (.591) | 0.8 (.031) |                        |         |
| >1 to 2.5                       | GSC-2.5  | 2.5          | 2.3 (.091)          | 15.0 (.591) | 0.8 (.031) |                        | 1,000   |
| >2.5 to 6                       | GSC-6    | 6            | 3.6 (.142)          | 15.0 (.591) | 1.0 (.039) | WC-0510DIN, WC-1016DIN | 500     |
| >6 to 10                        | GSC-10   | 10           | 4.5 (.177)          | 20.0 (.787) | 1.1 (.043) |                        |         |
| >10 to 16                       | GSC-16   | 16           | 5.8 (.228)          | 23.0 (.906) | 1.2 (.047) | —                      | 250     |
| >16 to 25                       | GSC-25   | 25           | 7.5 (.295)          | 25.0 (.984) | 1.5 (.059) |                        | 200     |
| >25 to 35                       | GSC-35   | 35           | 9.0 (.354)          | 27.0(1.063) | 1.6 (.063) |                        | 100     |
| >35 to 50                       | GSC-50   | 50           | 11.0 (.433)         | 38.0(1.496) | 1.8 (.071) |                        | 100     |
| >50 to 70                       | GSC-70   | 70           | 13.0 (.512)         | 42.0(1.654) | 2.0 (.079) |                        | 50      |
| >70 to 95                       | GSC-95   | 95           | 15.0 (.591)         | 48.0(1.890) | 2.5 (.098) |                        | 50      |
| >95 to 120                      | GSC-120  | 120          | 16.5 (.650)         | 52.0(2.047) | 3.0 (.118) |                        | 25      |
| >120 to 150                     | GSC-150  | 150          | 19.0 (.748)         | 56.0(2.205) | 3.2 (.126) |                        |         |

Note: 1) Contact J.S.T.(U.K.) Ltd for the above tools.  
 2) Reference: DIN46341 Contact J.S.T. DEUTSCHLAND GMBH for details.  
 3) Delivery lead times may vary depending on the product. Contact JST for details.



**Vinyl-insulated**

| Applicable Wire mm <sup>2</sup> | Part No.  | Nominal Size | Dimensions mm (in.) |                   |             |             |            | Color  | Tool No.   | Qty/box |
|---------------------------------|-----------|--------------|---------------------|-------------------|-------------|-------------|------------|--------|------------|---------|
|                                 |           |              | $\varnothing d_1$   | $\varnothing d_2$ | $\ell_1$    | $\ell_2$    | s          |        |            |         |
| 0.5 to 1                        | FVGSC-1   | 1            | 1.6 (.063)          | 3.4 (.134)        | 15.0 (.591) | 25.0 (.984) | 0.8 (.031) | Red    | WC-2210DIN | 1,000   |
| >1 to 2.5                       | FVGSC-2.5 | 2.5          | 2.3 (.091)          | 4.3 (.169)        | 15.0 (.591) | 25.0 (.984) | 0.8 (.031) | Blue   | WC-2210DIN | 1,000   |
| >2.5 to 6                       | FVGSC-6   | 6            | 3.6 (.142)          | 6.4 (.252)        | 15.0 (.591) | 27.0(1.063) | 1.0 (.039) | Yellow | WC-2210DIN | 500     |

Note: 1) Contact J.S.T.(U.K.) Ltd for the above tools.  
 2) Reference: DIN46341 Contact J.S.T. DEUTSCHLAND GMBH for details.  
 3) Delivery lead times may vary depending on the product. Contact JST for details.

**Nylon-insulated**

| Applicable Wire mm <sup>2</sup> | Part No.  | Nominal Size | Dimensions mm (in.) |                   |             |             |            | Color  | Tool No.   | Qty/box |
|---------------------------------|-----------|--------------|---------------------|-------------------|-------------|-------------|------------|--------|------------|---------|
|                                 |           |              | $\varnothing d_1$   | $\varnothing d_2$ | $\ell_1$    | $\ell_2$    | s          |        |            |         |
| 0.1 to <0.5                     | FNGSC-0.5 |              | 1.2 (.047)          | 2.0 (.079)        | 12.0 (.472) | 20.0 (.787) | 0.4 (.016) | Yellow | —          | 2,000   |
| 0.5 to 1                        | FNGSC-1   | 1            | 1.6 (.063)          | 3.2 (.126)        | 15.0 (.591) | 25.0 (.984) | 0.8 (.031) | Red    | WC-2210DIN | 1,000   |
| >1 to 2.5                       | FNGSC-2.5 | 2.5          | 2.3 (.091)          | 3.8 (.150)        | 15.0 (.591) | 25.0 (.984) | 0.8 (.031) | Blue   | WC-2210DIN | 1,000   |
| >2.5 to 6                       | FNGSC-6   | 6            | 3.6 (.142)          | 5.4 (.213)        | 15.0 (.591) | 27.0(1.063) | 1.0 (.039) | Yellow | WC-2210DIN | 500     |

Note: 1) Contact J.S.T.(U.K.) Ltd for the above tools.  
 2) Reference: DIN46341 Contact J.S.T. DEUTSCHLAND GMBH for details.  
 3) Delivery lead times may vary depending on the product. Contact JST for details.