
# **BULLET** TERMINAL

#### Nominal 4.0mm dia. bullet male




Recognized E60389

⑥ Certified LR20812

		1	Applicable wire	е			Dimensions(mm)					
Model No.	Standard	mm²	AWG #	Insulation O.D. (mm)	Material	Finish	D (dia.)	L	S	Material thickness	Q'ty / reel	
SGM-51-4	<b>71</b> @		<b>1</b>	20 to 14	2.6 to 3.8	Brass	_	3.55	15.9	7.3	0.5	F 000
SGM-51T-4		0.5 10 2.0	20 10 14	2.0 10 3.8	DidSS	Tin-plated	3.33	15.9	7.3	0.5	5,000	

RoHS compliance

## Nominal 4.0mm dia. bullet female




Recognized E60389

€ Certified LR20812

		,	Applicable wire	Э				Dimensi	ons(mm)			
Model No.	Standard	mm²	AWG #	Insulation O.D. (mm)	Material	Finish	D (dia.)	L	S	Material thickness	Q'ty / reel	
SGF-41-4	<b>71</b> @	<b>D</b> I 6 0540	0.5 to 1.25	00 1- 10	0.040.0.5	Dress		0.5	47.5	0.4	0.00	7.500
SGF-41T-4		0.5 (0 1.25	0.5 to 1.25   20 to 16   2.6 to 3.5   Brass	Brass	Tin-plated	3.5	17.5	6.4	0.32	7,500		

RoHS compliance

#### Nominal 5.0mm dia. bullet male




Recognized E60389

⊕ Certified LR20812

		,	Applicable wire					Dimensions(mm)				
Model No.	Standard	mm²	AWG #	Insulation O.D. (mm)	Material	Finish	D (dia.)	L	S	Material thickness	Q'ty / reel	
SGM-21-5		<b>71</b> ° @ 0.:	0.04-0.75	00 to 10	1.7 to 2.9		_					
SGM-21T-5	<b>77</b> @	0.3 to 0.75	22 to 18	1.7 10 2.9	Brass	Tin-plated	3.96	17.5	8.9	0.5	5,000	
SGM-51-5	<b>71</b> ®	<b>9</b> 0.5 to 2.0	20 to 14	2.6 to 3.8		_		17.5			3,000	
SGM-51T-5			1 UP 0.5 to 2.0 20 to 14 2.6 to 3.8		Tin-plated							

RoHS compliance

#### Nominal 5.0mm dia. bullet female



#### Recognized E60389

#### Certified LR20812

			Applicable	wire					Dimensi	ons(mm)				
Model No.	Standard	mm²	AWG #	Insulation O.D. (mm)	Material	Туре	Finish	D (dia.)	L	S	Material thickness	Q'ty / reel		
SGF-21-5		<b>91</b> ° <b>(</b> ) 0.3 to 0.75	75 22 to 18	1.7 to 2.9	- Brass	ass A	_	3.96		6.4	0.4			
SGF-21T-5	<b>A7</b> @						Tin-plated		17.5			5,000		
SGF-51-5	<b>A</b> •						_		17.5	0.4		5,000		
SGF-51T-5		0.5 to 2.0	20 to 14	2.6 to 3.8			Tin-plated							

### Crimping machine, Applicator

	Crimpina	Applicator						
Contact	Crimping machine	Crimp applicator	Dies	Crimp applicator with dies				
SGM-51(T)-4		MK-L	MK/SGM-51-4	APLMK SGM51-4				
	AP-K2N	_	_	_				
SGF-41(T)-4		MK-L	MK/SGF-41-4	APLMK SGF41-4				
3GF-41(1)-4		_	_	-				
SCM 21/T) 5		MK-L	MK/SGM-21-5	APLMK SGM21-5				
SGM-21(T)-5		_	_	_				

	Crimping	Applicator						
Contact		Crimp applicator	Dies	Crimp applicator with dies				
COM 54/T) 5		MK-L	MK/SGM-51-5	APLMK SGM51-5				
SGM-51(T)-5		_	_	-				
SGF-21(T)-5	AP-K2N	MK-L	MK/SGF-21-5	APLMK SGF21-5				
3GF-21(1)-5		-	-	-				
SCE E1/T) E		MK-L	MK/SGF-51-5	APLMK SGF51-5				
SGF-51(T)-5		_	_	_				

<sup>\*</sup> Compliant with RoHS.

<sup>\*</sup> Refer to "General Instruction and Notice when using Terminals and Connectors" at the end of this catalog.

<sup>\*</sup> Contact JST for details.